



# Certificate

The following products:

**DUPLEX**  
**ELO-RAYEX**  
**TV-RAYEX**  
**MINI-RAYONEX**  
**E-SMOG-RAYONATOR**  
**HF-RAYONATOR**

of the company RAYONEX Schwingungstechnik GmbH  
Sauerland-Pyramiden 1  
57368 Lennestadt  
GERMANY

were accurately examined in our institute regarding safety and efficacy.

We herewith confirm that the above listed products fulfill the highest demands related to electric safety and that no risks like emission of radiation or any other risks exist. The detailed results of our examination are listed below product by product:

## DUPLEX

The frequency spectra used in the DUPLEX devices reduce strains evoked by geopathy, underground watercourses, dislocations, Curry-nets, Hartman-grids and Benker-grids. The efficacy radius could be determined as following:

DUPLEX small: 4 m radius  
DUPLEX middle: 8 m radius  
DUPLEX big: 16 m radius

## TV-RAYEX

This device has only one (1) frequency value: 99,5.

We found out that this is not sufficient for a reduction of electro smog and consequently we can only partially recommend this device.

## ELO-RAYEX

In the ELO-RAYEX the six (6) most important basic frequency values are installed, able to reduce in particular electro smog in a close radius around humans (2 m radius).

## MINI-RAYONEX

In the MINI-RAYONEX the most important basic frequency value (12,5) for the stimulation of the energy household of humans is installed. As each strain of the human organism needs energy, the MINI-RAYONEX can be used in a very various way. We could determine an efficacy radius of 2,5 meters with the appropriate measuring technique.

## E-SMOG-RAYONATOR

The E-Smog-Rayonator contains, as the ELO-RAYEX does, the six (6) most important basic frequency values referring to electro smog. Contrary to the ELO-RAYEX, the E-SMOG- RAYONATOR delivers its frequencies via a connected DUPLEX. The efficacy radius we measured corresponds with the DUPLEX itself.

## HF-RAYONATOR

The HF-RAYONATOR minimizes, by totally 10 important basic frequency values, the damaging influences (like electro smog etc.) in the human organism by impulse modulation. The efficacy spectra in the HF-RAYONATOR correspond with the spectra we measured in the DUPLEX.



Head of Institute

Wolfgang Sievers, 04.06.2012



# 证书

以下产品：

Duplex 平衡塔  
电磁防护尺  
电视防护尺  
迷你能  
电磁辐射调和器  
高频调和器

来自瑞欧内克斯振动技术有限公司  
索尔兰金字塔1号  
57368 伦纳斯塔特市  
德国

其安全性及功效性已经过我们研究所精确的检测  
我们在此确认，上述产品符合与电器安全相关的最高要求，不存在如辐射或任何其他风险。我们检测的详细结果依照产品逐项列出如下：

## DUPLEX

DUPLEX装置中所使用的频谱可减少由地场压力、地下水道、错位、科利网、哈特曼网格和本克网格所引起的劳损。其有效半径可确定如下：

DUPLEX 小型：4米径  
DUPLEX 中型：8米径  
DUPLEX 大型：16米径

## 电视防护尺

此装置只有一（1）个频率值：99.5。

我们发现若要减少电子烟雾这是不够的，因此，我们只能部分推荐这个装置。

## 电磁防护尺

电磁防护尺中安装了六（6）个最重要的基本频率值，特别能够减少人体周围附近（2米半径）的电子烟雾。

## 迷你能

迷你能中安装了用于刺激人类居家能量最重要的基本频率值（12.5）。由于人类有机体的每种劳损都需要能量，因此迷你瑞欧克斯可以使用于非常多的方式。我们可以用适当的测量技术确定其2.5米的功效半径。

## 电磁辐射调和器

如同电磁防护尺，电磁辐射调和器包含六（6）个与电子烟雾相关最重要的基本频率值。与电磁防护尺不同的是，电磁辐射调和器通过连接的DUPLEX装置发射频率。我们测量到的功效半径与DUPLEX装置本身一样。

## 高频调和器

高频调和器中共有10个重要的基本频率值，可将人类有机体中因脉冲调制造成的有害影响（如电子烟雾等）降至最低。高频调和器的功效范围与我们在DUPLEX装置中测量到的范围一样。



研究所所长

沃夫冈·希瓦士 (Wolfgang Sievers), 04.06.2012